

# Product Datasheet

## ATA163019016



ATA163019016

Trunking 16x30,L=2,1m,traffic white

Technical Features

Dimensions

Height	30 mm
Width	16 mm
Length	2100 mm
Lid width	16 mm
Inner cross-section	420 - 420 mm²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	2
--	---

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 65 °C
-----------------------	------------

Connectivity

Trunking coupling	Without coupling
-------------------	------------------

Equipment

Number of partitions	1
Number of compartments	2 - 2
Number of pluggable partitions	0
Cable retaining clip included	Yes
With protective film	No

Installation, mounting

Base perforation	No
------------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

