



29526084



LED signal light, red/green lighting Q.x alu velvety, lacquered

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 0.50 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Aluminium

RAL code 9006

Surface finish Velvety

Material Metal
Plastic

Treatment Varnished

Dimensions

Height 70 mm

Width 70 mm

Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Connectivity

Mounting type Claw mounting
Screw connection

Safety

Ingress Protection (IP) class IP20

Texts

Labelling Foil bi-colour with imprinted symbols for Do not disturb / Make up room and Enter/ Wait are supplied

Imprint Without imprint

Suitable for

Q.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes