



29526086



LED signal light, red/green lighting, Q.x, ant. velvety, lacq.

**Technical Features**

**Voltage**

Rated voltage 230 V

**Power**

Power absorbed 0.50 W

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour Anthracite  
RAL code 7021  
Surface finish Velvety  
Material Metal  
Plastic  
Treatment Varnished

**Dimensions**

Height 70 mm  
Width 70 mm  
Depth 50 mm

**Connection**

Conductor cross-section 2.50 - 2.50 mm<sup>2</sup>

**Connectivity**

Mounting type Claw mounting  
Screw connection

**Safety**

Ingress Protection (IP) class IP20

**Texts**

Labelling Foil bi-colour with imprinted symbols for Do not disturb / Make up room and Enter/ Wait are supplied  
Imprint Without imprint

**Suitable for**

Q.x

**Sustainability**

Halogen free Yes  
REACH-SVHC free Yes  
RoHS conform Yes