



HCJ401AR



Load Break Switch Disconnecter h3 x630 4P 400A FTC

Technical Features

Electric current

Rated current	400 A
Rated short-time withstand current I _{cw} IEC 60947	5 kA

Architecture

Number of poles	4
Control/operation element	Toggle

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes