



HCJ401AR



Prekidač snage, h3+ x630, 4x400A

Tehničke karakteristike

Električna struja

Nazivna struja	400 A
Nazivna kratkotrajna podnosiva struja I _{cw} IEC 60947	5 kA

Arhitektura

Broj polova	4
Kontrolni/radni element	Okretna preklopna tipka

Napon

Nazivni izolacijski napon U _i	800 V
Nazivni impulsni podnosivi napon U _{imp}	8000 V

Frekvencija

Frekvencija	50 - 60 Hz
-------------	------------

Funkcije

Zaštitna/trip jedinica	Prekidač
------------------------	----------

Održivost

REACH-bez SVHC	Da
Usklađeno sa RoHS	Da