



REK350X



Sub-line coupler inclusiv power supply 2wire video bus system RMD

Technical Features

Capacity

Number of modules 10

Installation, mounting

Mounting on DIN rail

Use conditions

Operating temperature 5 - 40 °C

Storage/transport temperature -20 - 60 °C

Materials

Colour Light grey

Safety

Ingress Protection (IP) class IP20

Connection

Conductor cross-section 0 - 0 mm²

Functions

Function Extending

Sustainability

RoHS conform Yes