



REN090X



**Status indication module built-in 2-wire stainless steel matt modesta**

**Technical Features**

**Materials**

Colour	Stainless steel
Material	Metal
Surface finish	Matt

**Dimensions**

Dimensions	120 x 120 mm
Height	120 mm
Width	120 mm
Built-in depth	22.50 mm

**Voltage**

Operating voltage	24 - 24 V
-------------------	-----------

**Controls and indicators**

Number of call buttons	0
------------------------	---

**Functions**

Function	Inform
----------	--------

**Settings**

Number of users	0
-----------------	---

**Use conditions**

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C