



41491404

SCHUKO soc.out.,lab.field,enhncd contact prot.,screw-in lift term.,B.7,al.lacq.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Aluminium
RAL code 9006
Surface finish Matt
Material Thermoplastic
Treatment Untreated Varnished

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth 32 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal
Mounting type Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid No
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field Yes

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes
Impact resistance IK IK05
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate
Protection Enhanced contact protection

Texts

Type of connection	With screw-in lift terminals
Labelling	With labelling field

Suitable for

S.x/B.x

Sustainability

RoHS conform	Yes
--------------	-----