

# Product Datasheet

## HIC490G



HIC425G

### Automatic transfer switch 4x 1000A

#### Technical Features

##### Voltage

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 380 - 415 V |
|------------------------------|-------------|

##### Electric current

|                                                              |        |
|--------------------------------------------------------------|--------|
| Rated current                                                | 1000 A |
| Rated conditional short-circuit current Icc with gl-gG fuses | 100 kA |

##### Power

|                                            |          |
|--------------------------------------------|----------|
| Rated operational power under 400 V AC AC1 | 658000 W |
|--------------------------------------------|----------|

##### Architecture

|                          |                |
|--------------------------|----------------|
| Number of poles          | 4              |
| Device construction type | Fixed built-in |

##### Compatibility

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | No  |
| Suitable for distribution board | Yes |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Mounting plate |
|-------------|----------------|