



FL558A

Steel counterdoor, Orion.Plus sheet metal, H1250 W600 mm

Technical Features

Dimensions

Height	1200 mm
Width	550 mm
Depth	20 mm

Cover, door

Door/cover is transparent	No
Number of cabinet doors	1
Cabinet door type	Inner door

Materials

RAL code	7035
Colour	Light grey
Material	Steel
Treatment	Galvanised

Safety

Ingress Protection (IP) class	IP65
Locking type	Double lock bar 3 mm