



TYA670WD2

Gateway KNX-DALI 2, tunable white, 4 modules

Technical Features

Equipment

Web server	Yes
------------	-----

Voltage

Operating voltage	240 - 240 V
Operating voltage over bus	21 - 32 V
Type voltage supply	DC

Connectivity

Type of interface bus system/media gateway	Light system interface/DALI
--	-----------------------------

Settings

Supported configuration mode	ETS
------------------------------	-----

Power

Power consumption VA	0,15 VA
----------------------	---------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Equipment

Number of channels	1
--------------------	---

Use conditions

Operating temperature	5 - 45 °C
-----------------------	-----------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Width	72 mm
Dimensions	90 x 72 mm
Depth	70 mm
Number of width units	4

Connection

Connector/plug type	DRA (DIN-rail Adapter)
---------------------	------------------------

Texts

Voltage	As DALI master and power supply for DALI devices
Type of connection	With screw terminals

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes