



WNC100

cubyko Socket 2P+E screwless wall mounted grey IP55

Technical Features

Electric current

Rated current	16 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt Satin finish
Material	Polycarbonate (PC) Polypropylene (PP)

Dimensions

Height	75 mm
Width	75 mm
Depth	22.80 mm
Number of units	1

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
With hinged lid	Yes

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

Functions

With orientation lighting	No
---------------------------	----

Identification

With imprint	No
--------------	----

Texts

Cover	For covering of socket outlets
Protection	Without protective screen

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes