



20306086



Thermostat, NC contact, centre plate, rocker switch, Q.1/Q.3, ant. velvety lacq.

Technical Features

Architecture

Control/operation element Rotative

Electric current

Rated current 4 A
Switching current 10 A
Max. switching current 10 A

Voltage

Nominal voltage 230-230 V

Power supply

Supply voltage 230 V AC

Frequency

Frequency 50 - 60 Hz

Settings

Comfort temperature setpoint 5 - 30 °C

Materials

Colour Anthracite
RAL code 7016
Surface finish Velvety
Material Metal
Plastic

Dimensions

Height 71 mm
Width 71 mm
Depth 50.90 mm

Screen

With display No

Equipment

Switching temperature difference 0.50 K
Type of thermostat Room thermostat
Type of probe Bimetal
With heater Yes

Safety

Ingress Protection (IP) class IP20

Connection

Type of contacts 1NC

Compatibility

Type of HVAC control Heating

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Without spreader claws
Type of connection With plug-in terminals
Thermal re-circulation With thermal return
Imprint With imprint
Junction With separate connection for night lowering

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes
