



HIC425E

**ATS with energy management 4x 1000A**

**Technical Features**

**Voltage**

Rated operational voltage $U_e$	380 - 415 V
---------------------------------	-------------

**Electric current**

Rated current	1000 A
Rated conditional short-circuit current $I_{cc}$ with gl-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	658000 W
--	----------

**Architecture**

Number of poles	4
Device construction type	Fixed built-in

**Compatibility**

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes