

# Product Datasheet

## WGDL131NB



WGDL131NB

### 16AX 3G 1W switch;nb

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 16 A |
|-------------------|------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | Bronze             |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Varnished          |

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

##### Dimensions

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 86 x 86 mm |
| Built-in depth flush-mounted boxes | 35 mm      |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Texts

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |