



SM200

Pulsed output module for SM102E

Technical Features

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 80 °C

Connection

Cross-section flexible conductor	0.5 - 1.5 mm ²
Cross-section rigid conductor	0.5 - 1.5 mm ²

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Voltage

Rated insulation voltage U _i	4000 V
---	--------

Dimensions

Height	84 mm
Width	21 mm
Depth	36 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes