



FP23TN2

Enclosure, univers, IP44, Protecion class1, 1950x800x205mm, empty

### Technical Features

#### Dimensions

|                       |         |
|-----------------------|---------|
| Height                | 1950 mm |
| Width                 | 800 mm  |
| Depth                 | 205 mm  |
| Thickness of sidewall | 1 mm    |

#### Safety

|                               |                          |
|-------------------------------|--------------------------|
| Ingress Protection (IP) class | IP44                     |
| Protection class              | Isolation class I        |
| Locking type                  | Bar lock<br>Without lock |
| Impact resistance IK          | IK09                     |

#### Equipment

|                                 |   |
|---------------------------------|---|
| Number of section in width      | 3 |
| Number of flange plate openings | 6 |

#### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Mounting on                | Floor mounting |
| Suitable for outdoor usage | No             |

#### Materials

|           |               |
|-----------|---------------|
| Colour    | Pure white    |
| RAL code  | 9010          |
| Treatment | Powder coated |
| Material  | Steel         |

#### Equipment

|                |    |
|----------------|----|
| Number of rows | 12 |
|----------------|----|

#### Materials

|                |      |
|----------------|------|
| Surface finish | Matt |
|----------------|------|

#### Cover, door

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 2  |
| Number of locks           | 1  |
| Door/cover is transparent | No |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 400 A |
|---------------|-------|

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|