



WGCC1REG

#### 1G frame (round);eg

##### Technical Features

###### Capacity

Number of gangs	1
Number of modules	0

###### Materials

Colour	Gold
Surface finish	Matt
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %
Treatment	Coated

###### Dimensions

Height	8 mm
Width	86 mm
Depth	8 mm
Number of units horizontal	1
Number of units vertical	1

###### Accessories

Has labelling field	No
---------------------	----

###### Installation, mounting

Mounting on	Mounting plate
-------------	----------------

###### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

###### Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

###### Sustainability

RoHS conform	Yes
--------------	-----