




WMGS13L

### 2 Way & Centre Off Latching Switch

#### Technical Features

##### Electric current

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Materials

|                |             |
|----------------|-------------|
| Colour         | White       |
| Surface finish | Glossy      |
| Material       | Duroplastic |
| Treatment      | Untreated   |

##### Identification

|                      |                                        |
|----------------------|----------------------------------------|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|----------------------------------------|

##### Connectivity

|               |                  |
|---------------|------------------|
| Mounting type | Snap-on mounting |
|---------------|------------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Dimensions

|                |            |
|----------------|------------|
| Dimensions     | 59 x 25 mm |
| Built-in depth | 13.10 mm   |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

##### Texts

|             |                                          |
|-------------|------------------------------------------|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole                                   |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |