



FL134AM

Steel enclosure, Orion.Plus, plain door 300x300x200 mm

Technical Features

Dimensions

Height	400 mm
Width	300 mm
Depth	200 mm
Thickness of sidewall	1.2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class I
Locking type	3-Side 7 mm
Impact resistance IK	IK10

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

Cover, door

Door/cover is transparent	No
---------------------------	----

Electric current

Rated current	250 A
---------------	-------

Sustainability

Halogen free	Yes
RoHS conform	Yes