



VU48NSG

Encl.,Volta,flush,4x12MOD,IP30,Version Singapore

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Electric current**

Rated current 63 A

**Power**

Maximum power loss per cabinet at  $\Delta T=20K$  27 W

**Equipment**

Number of rails 4

Number of rows 4

Number of section in width 1

With lock No

Has neutral terminal block Yes

**Capacity**

Number of modules 48

Number of half modules terminals per rail 96

**Functions**

With conduit inlets Yes

**Dimensions**

Height 755.50 mm

Width 348 mm

Depth 94.50 mm

Built-in height 740 mm

Built-in width 335 mm

**Cover, door**

Number of cabinet doors 1

**Dimensions**

Built-in depth 90 mm

**Cover, door**

Number of locks 0

**Dimensions**

Number of width units 12

**Cover, door**

Door/cover is transparent No

**Connectivity**

Mounting type Screw mounting

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

**Equipment**

Has earthing terminal block Yes

Has mounting plate No

---

**Materials**

---

|                       |     |
|-----------------------|-----|
| Ultraviolet-resistant | Yes |
|-----------------------|-----|

---

**Safety**

---

|                  |                    |
|------------------|--------------------|
| Protection class | Isolation class II |
|------------------|--------------------|

---

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP30 |
|-------------------------------|------|

---

|              |                              |
|--------------|------------------------------|
| Locking type | Snap on lock<br>Without lock |
|--------------|------------------------------|

---

|                |        |
|----------------|--------|
| Glow wire test | 650 °C |
|----------------|--------|

---

**Sustainability**

---

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

---