




WGCCH2NB

2G multi-gang frame (horizontal);nb

Technical Features

Capacity

Number of gangs	2
Number of modules	0

Materials

Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Contains recycled material (% of total plastic weight)	0 %
Treatment	Coated

Dimensions

Height	8 mm
Width	86 mm
Depth	8 mm

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Mounting plate
Mounting-/Connection Position	Front

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----