



47516066



SCHUKO soc. out. hinged cover, Q.x, ant. velvety, lacq.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Anthracite
RAL code 7021
Surface finish Velvety
Material Thermoplastic
Treatment Untreated Varnished

Dimensions

Height 71 mm
Width 71 mm
Number of units 1
Built-in depth flush-mounted boxes 35 mm
Built-in depth 32 mm

Connection

Connector/plug type Plug-in terminal

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid Yes
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field No

Cover, door

Type of lid Self-closing hinged cover

Capacity

Number of modules 1

Safety

With enhanced contact protection No
Impact resistance IK IK02
Ingress Protection (IP) class IP20

Functions

With orientation lighting No
With function lighting No

Texts

Imprint	With imprint
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

Q.x

Sustainability

RoHS conform	Yes
--------------	-----