



SM500

Analoge voltmeter 0-500V

Technical Features

Capacity

Number of modules	4
-------------------	---

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Power

Total power loss under IN	3.50 W
Power consumption VA	3 VA

Dimensions

Height	90 mm
Width	70 mm
Depth	54 mm

Measurement

Type of measuring instrument	Analog
------------------------------	--------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

Accuracy class	0.015
----------------	-------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Frequency

Frequency	45 - 65 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes