



WPSSU83FON

13A FCU Switched with LED Indicator and Flex Outlet & Back Box

Technical Features

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Materials

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Safety

Ingress Protection (IP) class IP20

Electric current

Rated current 13 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting With control LED for ON

Switch mode 2-pole

Sustainability

RoHS conform Yes