



WPSSU83FON

### 13A FCU Switched with LED Indicator and Flex Outlet & Back Box

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Grey
--------	------

Surface finish	Glossy
----------------	--------

Material	Steel
----------	-------

Treatment	Epoxy
-----------	-------

##### Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
------------	------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Electric current

Rated current	13 A
---------------	------

##### Texts

Installation mode	For flush-mounted and hollow wall mounting
-------------------	--

Lighting	With control LED for ON
----------	-------------------------

Switch mode	2-pole
-------------	--------

##### Sustainability

RoHS conform	Yes
--------------	-----