



FL530B

### Polyester floor standing enclosure, Orion.Plus, 600x1100x300 mm

#### Technical Features

##### Dimensions

|                       |         |
|-----------------------|---------|
| Height                | 600 mm  |
| Width                 | 1100 mm |
| Depth                 | 300 mm  |
| Thickness of sidewall | 1.50 mm |

##### Safety

|                               |                         |
|-------------------------------|-------------------------|
| Ingress Protection (IP) class | IP65                    |
| Protection class              | Isolation class II      |
| Locking type                  | 3-Side 7 mm<br>Key lock |
| Impact resistance IK          | IK08                    |

##### Equipment

|                                 |   |
|---------------------------------|---|
| Number of flange plate openings | 0 |
|---------------------------------|---|

##### Installation, mounting

|                            |                |
|----------------------------|----------------|
| Mounting on                | Floor mounting |
| Suitable for outdoor usage | Yes            |

##### Materials

|           |            |
|-----------|------------|
| Colour    | Light grey |
| RAL code  | 7035       |
| Treatment | Untreated  |
| Material  | Plastic    |

##### Equipment

|                |   |
|----------------|---|
| Number of rows | 3 |
|----------------|---|

##### Cover, door

|                           |     |
|---------------------------|-----|
| Number of cabinet doors   | 0   |
| Door/cover is transparent | Yes |

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|