



47893502



SCHUKO soc.out.hinged cover surf.-mtd, lock-identical lockings,W.1,p.wh.m.plas.

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	76 mm
Width	76 mm
Depth	65 mm
Built-in depth flush-mounted boxes	0 mm

Connection

Conductor cross-section	1.0 - 2.5 mm ²
-------------------------	---------------------------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	Yes

Accessories

Has labelling field	Yes
---------------------	-----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	1
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP55

Product Datasheet

47893502

Functions		
With orientation lighting		No
With function lighting		No
Texts		
Imprint		Without imprint
Cover		Complete housing
Protection		Enhanced contact protection
Type of connection		With plug-in terminals
Terminal	With Wago clip-in 2-wire connection terminal for wiring	
	With two clip-in places for Wago 2-wire connection terminals in the housing floor	
Sustainability		
Halogen free		Yes
RoHS conform		Yes