



HMW250JR

### Moulded Case Circuit Breaker h3+ P630 LSI 3P3D 250A 50kA FTC

#### Technical Features

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated current                                                                 | 250 A |
| Rated ultimate short-circuit breaking capacity Icu under 230 V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2 | 85 kA |
| Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2 | 50 kA |
| Rated ultimate short-circuit breaking capacity Icu under 415 V AC IEC 60947-2 | 50 kA |
| Breaking capacity on 1-pole for AC 230 V IEC 60947-2                          | 10 kA |
| Breaking capacity on 1-pole for AC 400 V IEC 60947-2                          | 10 kA |

##### Architecture

|                           |                 |
|---------------------------|-----------------|
| Number of poles           | 3               |
| Control/operation element | Toggle          |
| Device construction type  | Fixed built-in  |
| Neutral position          | Without neutral |

##### Tripping

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

##### Electric current

|                                                                               |       |
|-------------------------------------------------------------------------------|-------|
| Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2 | 12 kA |
| Rated service breaking capacity Ics under 220 V AC according to IEC 60947-2   | 85 kA |
| Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2   | 85 kA |
| Rated service breaking capacity Ics under 240 V AC according to IEC 60947-2   | 85 kA |
| Rated service breaking capacity Ics under 380 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 415 V AC according to IEC 60947-2   | 50 kA |
| Rated service breaking capacity Ics under 690 V AC according to IEC 60947-2   | 12 kA |
| Rated current 10°C according to IEC 60947                                     | 250 A |
| Rated current 15°C according to IEC 60947                                     | 250 A |
| Rated current 20°C according to IEC 60947                                     | 250 A |
| Rated current 25°C according to IEC 60947                                     | 250 A |
| Rated current 30°C according to IEC 60947                                     | 250 A |
| Rated current at 35°C according to IEC 60947                                  | 250 A |
| Rated current at 40°C according to IEC 60947                                  | 250 A |
| Rated current 45°C according to IEC 60947                                     | 250 A |
| Rated current 50°C according to IEC 60947                                     | 250 A |
| Rated current 55°C according to IEC 60947                                     | 250 A |
| Rated current at 60°C according to IEC 60947                                  | 250 A |
| Rated current 70°C according to IEC 60947                                     | 250 A |
| Rated current 65°C according to IEC 60947                                     | 250 A |

##### Settings

|                                                           |                   |
|-----------------------------------------------------------|-------------------|
| Ir1 current dial setting                                  | 90 A              |
|                                                           | 100 A             |
|                                                           | 110 A             |
|                                                           | 125 A             |
|                                                           | 140 A             |
|                                                           | 160 A             |
|                                                           | 180 A             |
|                                                           | 200 A             |
|                                                           | 225 A             |
|                                                           | 250 A             |
| Adjustment range short-term delayed short-circuit release | 122.85 - 2500.0 A |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Installation, mounting

|                               |            |
|-------------------------------|------------|
| Nominal tightening torque     | 18 - 18 Nm |
| Mounting-/Connection Position | Front      |

#### Voltage

|                                      |             |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 8000 V      |
| Rated insulation voltage Ui          | 800 V       |
| Rated operational voltage Ue         | 220 - 690 V |

#### Functions

|           |     |
|-----------|-----|
| Trip unit | LSI |
|-----------|-----|

#### Power

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 36.8 W |
| Power loss per pole at In | 12.3 W |

#### Equipment

|                                                         |   |
|---------------------------------------------------------|---|
| Number of auxiliary contacts as change-over contact     | 0 |
| Number of auxiliary contacts as normally closed contact | 0 |
| Number of auxiliary contacts as normally open contact   | 0 |

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

#### Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

#### Connection

|                     |          |
|---------------------|----------|
| Connector/plug type | Terminal |
|---------------------|----------|

#### Cable

|                |        |
|----------------|--------|
| Cable material | Copper |
|----------------|--------|

#### Use conditions

|                                                          |   |
|----------------------------------------------------------|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
|----------------------------------------------------------|---|

#### Dimensions

|        |        |
|--------|--------|
| Height | 260 mm |
| Width  | 140 mm |
| Depth  | 150 mm |

#### Controls and indicators

|                        |    |
|------------------------|----|
| Motor drive integrated | No |
|------------------------|----|

#### Compatibility

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | No  |
| Compatible with RDC AOB         | Yes |
| Suitable for distribution board | Yes |

#### Power supply

|                       |               |
|-----------------------|---------------|
| Position power supply | Bidirectional |
|-----------------------|---------------|

#### Electrical protection

|                                                 |       |
|-------------------------------------------------|-------|
| Long-time overload protection (ltd): delay (tr) | 0.5 s |
|                                                 | 1.5 s |
|                                                 | 2.5 s |
|                                                 | 5 s   |
|                                                 | 7.5 s |
|                                                 | 9 s   |
|                                                 | 10 s  |
|                                                 | 12 s  |
|                                                 | 14 s  |
|                                                 | 16 s  |
| Short-time protection (std): current (Isd)      | 1.5   |
|                                                 | 2     |
|                                                 | 3     |
|                                                 | 4     |
|                                                 | 5     |
|                                                 | 6     |
|                                                 | 7     |
|                                                 | 8     |
|                                                 | 10    |

Electrical protection

|                                                         |        |
|---------------------------------------------------------|--------|
| Short-time protection (std): delay (tsd)                | 50 ms  |
|                                                         | 100 ms |
|                                                         | 200 ms |
|                                                         | 300 ms |
|                                                         | 400 ms |
| Instantaneous protection (li): dial setting coefficient | 3      |
|                                                         | 4      |
|                                                         | 5      |
|                                                         | 6      |
|                                                         | 7      |
|                                                         | 8      |
|                                                         | 10     |
|                                                         | 11     |
|                                                         | 12     |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|