



HIC408A

**Motorized changeover switch 4P 80A 400V**

**Technical Features**

**Voltage**

Rated operational voltage Ue	380 - 415 V
------------------------------	-------------

**Electric current**

Rated current	80 A
Rated conditional short-circuit current Icc with gl-gG fuses	50 kA

**Power**

Rated operational power under 400 V AC AC1	52000 W
--	---------

**Architecture**

Number of poles	4
Device construction type	Fixed built-in

**Compatibility**

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes

**Installation, mounting**

Mounting on	DIN rail Mounting plate
-------------	----------------------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes