



VSR_SIZE_5

Design 50,12Way,High Integrity,100A Switch,2*100A 30mA RCCB

Technical Features

Installation, mounting

Mounting on Surface mounting

Architecture

Number of poles 2

Functions

Overvoltage protection Yes

Installation, mounting

Suitable for outdoor usage No

Capacity

Number of modules 12

Electric current

Rated current 100 A

Dimensions

Depth 105 mm

Height 284 mm

Width 467 mm

Thickness of sidewall 1 mm

Cover, door

Interlockable No

Door/cover is transparent No

Materials

RAL code 9010

Colour Pure white

Material Steel

Connection

Number of accessible phases 1

Equipment

Number of rows 1

Number of rails 1

Extension possible No

Safety

Impact resistance IK IK05

Ingress Protection (IP) class IP2XC