



HIC425E

**ATS with energy management 4x 1600A**

**Technical Features**

**Voltage**

Rated operational voltage Ue	380 - 415 V
------------------------------	-------------

**Electric current**

Rated current	1600 A
Rated conditional short-circuit current Icc with gl-gG fuses	100 kA

**Power**

Rated operational power under 400 V AC AC1	1053000 W
--	-----------

**Architecture**

Number of poles	4
Device construction type	Fixed built-in

**Compatibility**

Suitable for DIN Rail	Yes
Suitable for distribution board	Yes