



SM400

Analogue ammeter 0-400A indirect reading

Technical Features

Capacity

Number of modules

4

Measurement

Current measurement range

0 - 400 A

Use conditions

Operating temperature

-25 - 50 °C

Storage/transport temperature

-40 - 80 °C

Connection

Cross-section flexible conductor

1 - 6 mm²

Cross-section rigid conductor

1.5 - 10 mm²

Dimensions

Height

85 mm

Width

70 mm

Depth

54 mm

Measurement

Type of measuring instrument

Analog

Power

Power consumption VA

1.10 VA

Safety

Ingress Protection (IP) class

IP20

Installation, mounting

Mounting on

DIN rail

Functions

Accuracy class

0.015

Voltage

Rated insulation voltage Ui

2000 V

Frequency

Frequency

45 - 65 Hz

Power

Total power loss under IN

1.10 W

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes