



FL527B

**Polyester floor standing enclosure, Orion.Plus, 1200x850x300 mm**

**Technical Features**

**Dimensions**

Height	1200 mm
Width	850 mm
Depth	300 mm
Thickness of sidewall	1.50 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	Barrel lock Key lock
Impact resistance IK	IK08

**Equipment**

Number of flange plate openings	0
---------------------------------	---

**Installation, mounting**

Mounting on	Floor mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Polyester

**Equipment**

Number of rows	7
----------------	---

**Cover, door**

Number of cabinet doors	0
Door/cover is transparent	No

**Electric current**

Rated current	250 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----