



KDN263B

**Insulated busbar 2P 63A fork 10mm<sup>2</sup> 57M**

**Technical Features**

**Electric current**

Rated current 63 A

**Architecture**

Number of poles 2

**Dimensions**

Length 1000 mm

**Voltage**

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 230 - 400 V

**Connection**

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

**Capacity**

Number of modules 56

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes