



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical Features

Electric current

Rated current	63 A
---------------	------

Architecture

Number of poles	2
-----------------	---

Dimensions

Length	1000 mm
--------	---------

Voltage

Rated impulse withstand voltage Uimp	4500 V
--------------------------------------	--------

Rated operational voltage Ue	230 - 400 V
------------------------------	-------------

Connection

Cross-section rigid conductor	10 mm ²
-------------------------------	--------------------

Connector/plug type	Phase busbar with fork
---------------------	------------------------

Capacity

Number of modules	56
-------------------	----

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----