



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical Features

Electric current	
Rated current	63 A
Architecture	
Number of poles	2
Dimensions	
Length	1000 mm
Voltage	
Rated impulse withstand voltage Uimp	4500 V
Rated operational voltage Ue	230 - 400 V
Connection	
Cross-section rigid conductor	10 mm²
Connector/plug type	Phase busbar with fork
Capacity	
Number of modules	56
Sustainability	
Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes