



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Dimensions

| | |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

Voltage

| | |
|--------------------------------------|-------------|
| Rated impulse withstand voltage Uimp | 4500 V |
| Rated operational voltage Ue | 230 - 400 V |

Connection

| | |
|-------------------------------|------------------------|
| Cross-section rigid conductor | 10 mm ² |
| Connector/plug type | Phase busbar with fork |

Capacity

| | |
|-------------------|----|
| Number of modules | 56 |
|-------------------|----|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |