



IU72MS

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	4
Number of rows	4

Capacity

Number of modules	72
-------------------	----

Dimensions

Height	782 mm
Width	475 mm
Depth	115 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	110 mm
----------------	--------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	18
-----------------------	----

Cover, door

Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	4
--------------------------	---

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Equipment

Has mounting plate	No
--------------------	----

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP40
Locking type	Without lock
Protection class with door	IP40

Sustainability

RoHS conform	Yes
--------------	-----