



VS212PTQ

Small distributor,golf,surface,2row,IP40,24M,QC-terminal,N+PE,white door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	24
-------------------	----

Dimensions

Height	377 mm
Width	282 mm
Depth	99 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C