



EP071

Auxiliary contact 1NC+NO

Technical Features

Electric current

Rated current	2 A
---------------	-----

Voltage

Rated insulation voltage Ui	250 V
-----------------------------	-------

Capacity

Number of modules	0.50
-------------------	------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 4 mm ²
Cross-section rigid conductor	1 - 6 mm ²
Type of contacts	1NC+1NO

Power

Total power loss under IN	0.40 W
---------------------------	--------

Dimensions

Height	85 mm
Width	8.75 mm
Depth	58 mm

Illustrations | Drawings

