



WMCC50

13A Double Pole Switched Socket Outlet with Cooker Control Unit

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	45 A
---------------	------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Dimensions

Height	86 mm
Width	146 mm
Depth	39.60 mm

Connection

Conductor cross-section	16 - 16 mm ²
-------------------------	-------------------------

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	Yes

Identification

With imprint	No
--------------	----

Texts

Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes