



WGDL132EG

**16AX 3G 2W switch;eg**

**Technical Features**

**Electric current**

Switching current	16 A
-------------------	------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	Gold
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	3
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Triple rocker
---------------------------	---------------

**Electric current**

Rated current	16 A
---------------	------

**Texts**

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes