



WGDL132EG

### 16AX 3G 2W switch;eg

#### Technical Features

##### Electric current

Switching current	16 A
-------------------	------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Gold
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	3
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Triple rocker
---------------------------	---------------

##### Electric current

Rated current	16 A
---------------	------

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes