

# Product Datasheet

## JHF812BG



JHF812BG

### 800A 12 Way Panelboard 125A Glazed Door

#### Technical Features

##### Connection

Number of accessible phases	3
-----------------------------	---

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Electric current

Rated current	800 A
---------------	-------

##### Equipment

With lock	Yes
Has neutral terminal block	Yes

##### Capacity

Number of modules	12
-------------------	----

##### Dimensions

Height	2050 mm
Width	900 mm
Depth	220 mm

##### Cover, door

Number of cabinet doors	1
Door/cover is transparent	Yes

##### Materials

Material	Steel
RAL code	7035
Colour	Light grey

##### Equipment

Has earthing terminal block	Yes
-----------------------------	-----

##### Safety

Protection class	Isolation class I
Ingress Protection (IP) class	IP2XC
Locking type	Quarter turn lock

##### Sustainability

RoHS conform	Yes
--------------	-----