



WFPS32BSW

10AX 3 Gang 2 Way Wall Switch Brushed Steel White Insert

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Stainless steel

Surface finish Matt

Material Stainless steel

Treatment Brushed

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 3

Dimensions

Dimensions 86 x 86 mm

Built-in depth 19.10 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Triple rocker

Electric current

Rated current 10 A

Texts

Installation mode For flush-mounted and hollow wall mounting

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes