



85745124



KNX radio blind time switch quicklink Q.x alu velvety, lacquered

Technical Features

Settings

| | |
|------------------------------|-----------|
| Supported configuration mode | quicklink |
|------------------------------|-----------|

Connectivity

| | |
|---------------------------|-----------|
| With bus system KNX radio | Yes |
| Radio protocol | KNX Radio |

Equipment

| | |
|--------------------|---|
| Number of channels | 2 |
|--------------------|---|

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Equipment

| | |
|-------------------------------|-----|
| Summer-/wintertime switchover | Yes |
|-------------------------------|-----|

Functions

| | |
|------------------------|-------|
| Runtime | 2 min |
| Astro time shift | 2 h |
| Battery backup | 8 h |
| Power reserve in years | 0 y |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Materials

| | |
|--------|-----------|
| Colour | Aluminium |
|--------|-----------|

Texts

| | |
|------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Function | Easy additional functions: +6 scenes, 1 up/down operating mode Configurable transmission and/or reception behaviour With keylock Party function, no execution of automatic, radio and extension unit commands (lock-out protection) Reset function (to factory setting) |
| Protection | With dismantling protection |

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Dimensions

| | |
|--------|----------|
| Height | 58.40 mm |
| Width | 58.40 mm |
| Depth | 30 mm |