



HIC425G

Automatic transfer switch 4x 2000A

Technical Features

Voltage

|                              |             |
|------------------------------|-------------|
| Rated operational voltage Ue | 380 - 415 V |
|------------------------------|-------------|

Electric current

|               |        |
|---------------|--------|
| Rated current | 2000 A |
|---------------|--------|

Power

|                                            |           |
|--------------------------------------------|-----------|
| Rated operational power under 400 V AC AC1 | 1316000 W |
|--------------------------------------------|-----------|

Architecture

|                          |                |
|--------------------------|----------------|
| Number of poles          | 4              |
| Device construction type | Fixed built-in |

Compatibility

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | No  |
| Suitable for distribution board | Yes |

Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Mounting plate |
|-------------|----------------|