


Product Datasheet

WGDL132IG



WGDL132IG

16AX 3G 2W switch;ig

Technical Features

Electric current	
Switching current	16 A

Installation, mounting	
Mounting on	Flush mounting

Voltage	
Rated voltage	250 V

Materials	
Colour	Interstellar grey
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Connectivity	
Mounting type	Screw mounting

Controls and indicators	
Number of buttons	3

Dimensions	
Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm

Safety	
Ingress Protection (IP) class	IP20

Architecture	
Control/operation element	Triple rocker

Electric current	
Rated current	16 A

Texts	
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes