

Product Datasheet

WGDL132NB



WGDL132NB

16AX 3G 2W switch;nb

Technical Features

Electric current	
Switching current	16 A
Voltage	
Rated voltage	250 V
Materials	
Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Controls and indicators	
Number of buttons	3
Dimensions	
Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm
Safety	
Ingress Protection (IP) class	IP20
Architecture	
Control/operation element	Triple rocker
Electric current	
Rated current	16 A
Texts	
Switch mode	2-way
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes